

Non-isolation type low price high precision analog output board for Low Profile PCI

**DA16-4(LPCI)L**



\* Specifications, color and design of the products are subject to change without notice.

**Features**

**Rich set of basic functions**

Compact system providing high-precision analog outputs. This product is a control signal(3 points) of analog output(16bits, 4ch), analog output. Digital inputs (four channels), digital outputs (four channels), and a counter (32-bit one channel).

**Substantial control functions**

Capable of analog output in time-based mode or external-signal synchronous mode.

**Filter function facilitating external signal connection**

Digital filters provided for external control analog output signals, preventing chattering

**Buffer memory**

The analog outputs each have their own buffer memory. You can also perform analog output in the background, independent of software and the current status of the PC.

**Software-based calibration function**

Calibration of analog output can be all performed by software. Apart from the adjustment information prepared before shipment, additional adjustment information can be stored according to the use environment.

**Exchangeable low-profile and standard PCI slots**

Support for both of low-profile and standard PCI slots (interchangeable with a bundled bracket).

**Plug-ins for the dedicated libraries, the board also supports MATLAB and LabVIEW.**

We offer a dedicated library [ML-DAQ], which allows you to use this product on MATLAB by The MathWorks as well as another dedicated library [VI-DAQ], which allows you to use the product on LabVIEW.

These dedicated libraries are available, free of charge (downloadable), on our web site.

This product is a PCI-compliant interface board that incorporates high-precision analog outputs, digital inputs, digital outputs, and a counter function.

The board can make your space-saving PC into a cost-effective analog output system.

You can use the driver library (API-PAC(W32)) supplied with the board to write Windows application programs in any programming language (such as Visual Basic, Visual C++, etc.) that supports the calling of Win32 API functions.

It can also collect data easily without a program when the data logger software [C-LOGGER] stored on the attached CD-ROM is used. With plug-ins for the dedicated libraries, the board also supports MATLAB and LabVIEW.


**Specification**

Item	Specification
<b>Analog output</b>	
Isolated specification	Unisolated
Number of output channels	4ch
Output range	Bipolar $\pm 10V$
Absolute max. output current	$\pm 3mA$
Output impedance	$1\Omega$ or less
Resolution	16bit
Non-Linearity error *1	$\pm 5LSB$
Conversion speed	10 $\mu$ sec
Buffer memory	1k Word
Conversion start trigger	Software / external trigger
Conversion stop trigger	Number of sampling times / external trigger/software
External start signal	TTL level (Rising or falling edge can be selected by software) Digital filter (1 $\mu$ sec can be selected by software)
External stop signal	TTL level (Rising or falling edge can be selected by software) Digital filter (1 $\mu$ sec can be selected by software)
External clock signal	TTL level (Rising or falling edge can be selected by software)
<b>Digital I/O</b>	
Number of input channels	Unisolated input 4ch (TTL level positive logic)
Number of output channels	Unisolated output 4ch (TTL level positive logic)
<b>Counter</b>	
Number of channels	1ch
Counting system	Up count
Max. count	FFFFFFFFh (Binary data,32bit)
Number of external inputs	2 TTL level levels (Gate/Up)/ch Gate (High level), Up (Rising edge)
Number of external outputs	TTL level Count match output (positive logic, pulse output)
Response frequency	10MHz (Max.)
<b>Common section</b>	
I/O address	64 ports
Interruption level	Errors and various factors, One interrupt request line as INTA
Connector	10250-52A2JL(3M)
Power consumption	5VDC 440mA (Max.)
Operating condition	0 - 50°C, 10 - 90%RH (No condensation)
PCI bus specification	32bit, 33MHz, Universal key shapes supported *2
Dimension (mm)	121.69 (L) x 63.41 (H)
Weight	60g

\*1 The non-linearity error means an error of approximately 0.1% occurs over the maximum range at 0°C and 50°C ambient temperature.

\*2 This board requires power supply at +5V from an expansion slot (it does not work on a machine with a +3.3V power supply alone).

**Board Dimensions**



The standard outside dimension(L) is the distance from the end of the board to the outer surface of the slot cover.

## Support Software

### Windows version of analog I/O driver API-AIO(WDM)

**[Stored on the bundled CD-ROM driver library API-PAC(W32)]**

The API-AIO(WDM) is the Windows version driver library software that provides products in the form of Win32 API functions (DLL). Various sample programs such as Visual Basic and Visual C++, etc and diagnostic program useful for checking operation is provided.

< Operating environment >

OS Windows Vista, XP, Server 2003, 2000  
Adaptation language Visual Basic, Visual C++, Visual C#, Delphi, C++ Builder

You can download the updated version from the CONTEC's Web site (<http://www.contec.com/apipac/>). For more details on the supported OS, applicable language and new information, please visit the CONTEC's Web site.

### Linux version of analog I/O driver API-AIO(LNX)

**[Stored on the bundled CD-ROM driver library API-PAC(W32)]**

The API-AIO(LNX) is the Linux version driver software which provides device drivers (modules) by shared library and kernel version. Various sample programs of gcc are provided.

< Operating environment >

OS RedHatLinux, TurboLinux  
(For details on supported distributions, refer to Help available after installation.)

Adaptation language gcc

You can download the updated version from the CONTEC's Web site (<http://www.contec.com/apipac/>). For more details on the supported OS, applicable language and new information, please visit the CONTEC's Web site.

### Data Logger Software C-LOGGER

**[Stored on the bundled CD-ROM driver library API-PAC(W32)]**

C-LOGGER is a data logger software program compatible with our analog I/O products. This program enables the graph display of recorded signal data, zoom observation, file saving, and dynamic transfer to the spreadsheet software "Excel". No troublesome programming is required.

CONTEC provides download services (at <http://www.contec.com/clogger>) to supply the updated drivers. For details, refer to the C-LOGGER Users Guide or our website.

< Operating environment >

OS Windows Vista, XP, Server 2003, 2000

### Data Acquisition library for MATLAB ML-DAQ

**(Available for downloading (free of charge) from the CONTEC web site.)**

This is the library software which allows you to use our analog I/O device products on MATLAB by the MathWorks. Each function is offered in accordance with the interface which is integrated in MATLAB's Data Acquisition Toolbox.

See <http://www.contec.com/mldaq/> for details and download of ML-DAQ.

### Data acquisition VI library for LabVIEW VI-DAQ

**(Available for downloading (free of charge) from the CONTEC web site.)**

This is a VI library to use in National Instruments LabVIEW. VI-DAQ is created with a function form similar to that of LabVIEW's Data Acquisition VI, allowing you to use various devices without complicated settings.

See <http://www.contec.com/vidaq/> for details and download of VI-DAQ.

## Cable & Connector

### Cable (Option)

Shield Cable with 50-Pin Mini-Ribbon Connectors  
at either Ends : PCB50PS-0.5P (0.5m)  
: PCB50PS-1.5P (1.5m)

Shield Cable with 50-Pin Mini-Ribbon Connector  
at one End : PCA50PS-0.5P (0.5m)  
: PCA50PS-1.5P (1.5m)

## Accessories

### Accessories (Option)

Screw Terminal Unit (M3 x 50P) : EPD-50A \*1 \*6  
BNC Terminal Unit (for analog input 8ch): ATP-8L \*1\*5

\*1 PCB50PS-0.5P or PCB50PS-1.5P optional cable is required separately.  
\*5 Capable of using the analog input of up to 8ch, and analog output of up to 2ch.  
\*6 "Spring-up" type terminal is used to prevent terminal screws from falling off.


\* Check the CONTEC's Web site for more information on these options.

## Packing List

Board [DA16-4(LPCI)L] ... 1  
First step guide ... 1  
CD-ROM \*1 [API-PAC(W32)] ... 1  
Standard size bracket ... 1

\*1 The CD-ROM contains the driver software and User's Guide.


## Block Diagram



## How to connect the connectors

### Connector shape

To connect an external device to this board, plug the cable from the device into the interface connector (CN1) shown below.



\* Please refer to page 2 for more information on the supported cable and accessories.

### Connector Pin Assignment

#### Pin Assignments of Interface Connector(CN1)

Analog Output 02	AO 02	50	25	AO 00	Analog Output 00
Analog Ground (for AO)	AGND	49	24	AGND	Analog Ground (for AO)
Analog Output 03	AO 03	48	23	AO 01	Analog Output 01
Analog Ground (for AO)	AGND	47	22	AGND	Analog Ground (for AO)
Non Connect	N.C.	46	21	N.C.	Non Connect
Non Connect	N.C.	45	20	N.C.	Non Connect
Non Connect	N.C.	44	19	N.C.	Non Connect
Non Connect	N.C.	43	18	N.C.	Non Connect
Non Connect	N.C.	42	17	N.C.	Non Connect
Non Connect	N.C.	41	16	N.C.	Non Connect
Non Connect	N.C.	40	15	N.C.	Non Connect
Non Connect	N.C.	39	14	N.C.	Non Connect
Non Connect	N.C.	38	13	N.C.	Non Connect
Non Connect	N.C.	37	12	N.C.	Non Connect
AO External Start Trigger Input	AO START	36	11	N.C.	Non Connect
AO External Stop Trigger Input	AO STOP	35	10	N.C.	Non Connect
AO External Sampling Clock Input	AO EXCLK	34	9	N.C.	Non Connect
Digital Ground	DGND	33	8	DGND	Digital Ground
Digital Output 00	DO 00	32	7	DI 00	Digital Input 00
Digital Output 01	DO 01	31	6	DI 01	Digital Input 01
Digital Output 02	DO 02	30	5	DI 02	Digital Input 02
Digital Output 03	DO 03	29	4	DI 03	Digital Input 03
Digital Ground	DGND	28	3	DGND	Digital Ground
Counter UP Clock Input	CNT UPCLK	27	2	CNT GATE	Counter Gate Control Input
Reserved	Reserved	26	1	CNT OUT	Counter Output

Analog Output00 - Analog Output03	Analog output signal. The numbers correspond to channel numbers.
Analog Ground	Common analog ground for analog I/O signals.
AO External Start Trigger Input	External trigger input for starting analog output sampling.
AO External Stop Trigger Input	External trigger input for stopping analog output sampling.
AO External Sampling Clock Input	External sampling clock input for analog output.
Digital Input00 - Digital Input03	Digital input signal.
Digital Output00 - Digital Output03	Digital output signal.
Counter Gate Control Input	Gate control input signal for counter.
Counter Up Clock Input	Count-up clock input signal for counter.
Counter Output	Counter output signal.
Digital Ground	Common digital ground for digital I/O signals, external trigger inputs, external sampling clock inputs, and counter I/O signals.
Reserved	Reserved pin.
N.C.	No connection to this pin.

#### CAUTION

Do not connect any of the outputs and power outputs to the analog or digital ground. Neither connect outputs to each other. Doing either can result in a fault.

If analog and digital ground are shorted together, noise on the digital signals may affect the analog signals. Accordingly, analog and digital ground should be separated.


Leave "Reserved" pins unconnected. Connecting these pins may cause a fault in the board.

## Analog Output Signal Connection

This section shows how to connect the analog output signal by using a flat cable or a shielded cable.


The following figure shows an example of flat cable connection. Connect the signal source and ground to the CN1 analog output.

### Analog Output Connection (Flat Cable)



The following figure shows an example of shield cable connection. Use shielded cable if the distance between the signal source and board is long or if you want to provide better protection from noise. For each analog input channel on CN1, connect the core wire to the signal line and connect the shielding to ground.

### Analog Output Connection (Shield Cable)



\* The number of channels depends on each board. This product has four channels.

#### CAUTION

If the board or the connected wire receives noise, or the distance between the board and the target is long, data may not be outputted properly.

For analog output signal, the current capacity is  $\pm 3\text{mA}$  (Max.). Check the specification of the connected device before connecting the board.

Do not short the analog output signal to analog ground, digital ground, and/or power line. Doing so may damage the board.


Do not connect an analog output signal to any other analog output, either on the board or on an external device, as this may cause a fault on the board.

## Digital I/O signals, Counter signals and Control signals Connection


The following sections show examples of how to connect digital I/O signals, counter I/O signals, and other control I/O signals (external trigger input signals, sampling clock input signals, etc.).

All the digital I/O signals and control signals are TTL level signals.

### Digital Input Connection



### Digital Output Connection



### About the counter input control signal

Counter Gate Control Input (refer to the page 3 Connector Pin Assignment) acts as an input that validate or invalidate the input of an external clock for the counter. This function enables the control of an external clock input for the counter. The external clock for the counter is effective when input is "High", and invalid when input is "Low". If unconnected, it is a pull-up in the board (card) and remains "High". Therefore the external clock for the counter is effective when the counter gate control input is not connected.

#### CAUTION

Do not short the output signals to analog ground, digital ground, and/or power line. Doing so may damage the board.